Articles

Cat. No

Description

DAIHAN-brand<sup>®</sup> New-generation Digital Shaker, Orbital or Reciprocating, "MaXshake<sup>TM</sup>", Adjustable 2×Size Platforms, 10~300 rpm with Programmable func., Large LCD display, Quiet & Low-vibration, Available Rubber Mat-/Universal-Platform(Optional), without Platform 디지털 쉐이커, 2×사이즈 플랫폼 사용 가능, 저소음/저진동 긴 수명, 부드러운 시동 동작 및 속도 조절 (文文)

■ Made in Korea




(a) Digital Shaker Orbital-motion "MaXshake OB2" with w295×d295mm Rubber Mat Platform




(b) Digital Shaker Reciprocating-motion "MaXshake RP2" with w346×d346mm Universial Platform

## Optional Platforms/Spring Rack



(1) Universal Platform



(2) Rubber Mat Platform



(3) Universial Spring Rack



(4) Platform for Round Flask

## ■ PL(Product Liability) Insurance

- with Certificate & Traceability : Controlled by Serial Number, Certificate, Delivery-information, and Traceable Data Base System
- Ideal for Culturing Cells to Hybridization, Staining and Destaining Gels, Chemistry
- Patented Jog-Shuttle Control System \* Variable accessories are available (Optional)
- \* Hybridization, Washing Blots, Culturing Microbes
- \* Compact design easily fits in incubators and on the laboratory bench.
- \* Soft start and noise-free operation. \* Digital speed control easily adjusts from 10 to 300 rpm.
- \* Built-in digital timer. Use in continuous shaking or timer mode up to 99 hr 59 min.
- \* Gentle speed up and slow down by PID speed control. Slow start motion decreases risk of spills.
- \* Large LCD for speed and time adjustment, makes it possible to read the speed, timer function and operating mode.
- \* Low vibration, low noise
- \* Clearly laid out control panel for easyoperation.
- \* Speed regulation by microprocessor.
- \* Excellently applicable for continuousoperation.
- \* Constant speed independent ofload.
- \* Comprehensive range of accessories.
- \* Audible buzzer alarms on timeexpiration and when an error occurs.
- \* Over-speed detection and protection. \* Automatic recovery from power break.
- \* Brushless motor provides maintenance free operation.

## Specifications & Ordering information

Spec.	Model	(a) "MaXshake OB2"	(b) "MaXshake RP2"
Shaking Platform Size		255×255 mm	
Shaking Motion		Orbital Motion	Reciprocating Motion
Speed Range & Max. Load		10 ~ 300 rpm, 10kg	
Amplitude of Rotation (mm)		10 mm	
Motor		Brushless DC Motor	
Permissible Temp. & Moisture		Ambient +5 ~ 50 °C , 80%	
Timer & Alarm		99hr 59min (with Continuous run.), Error status & Timer-end	
Display		Large Size Digital LCD with Back-Light Function	
Controller		Digital Fuzzy Controller with Touch Button, Jog-dial	
Program Function		10 Steps, 6 Programs	
Platform		Universal Platform for various Shapes & Size of Flask	
Max. Capacity of Flask Holder	For 100ml	Standard by 251 × 251mm Universial Platform : 9 ea Flask Holders	
		Standard by 346 × 346mm Universial Platform : 20 ea Flask Holders	
	For 250ml	Standard by 251 × 251mm Universial Platform : 7 ea Flask Holders	
		Standard by 346 × 346mm Universial Platform : 15 ea Flask Holders	
	For 500ml	Standard by 251×251mm Universial Platform : 5 ea Flask Holders	
		Standard by 346 × 346mm Universial Platform : 9 ea Flask Holders	
	For 1000ml	Standard by 251×251mm Universial Platform : 4 ea Flask Holders	
		Standard by 346×346mm Universial Platform : 6 ea Flask Holders	
Dimension & Weight		376×375×h138 mm(Base Platfrom : 255×255 mm), 13kg	
Packing Dimension & Weight		345×420×h205 mm, 13.5kg	
Safety Circuit		Overload Protector for Motor	
Power Consumption		45 W	
Electrical Reqts.		1 Phase, AC 120V, 60Hz or AC 230V, 50 / 60Hz	
Cat. No.	230V	DH.WSO00300	DH.WSR00300
	120V	DH.WSO00301	DH.WSR00301
Price, Each. ₩		763,000	763,000
. Other Cresification		a unan Cuatamaria Daguast	W COLOLW 0 000 HITL

\* Other Specifications are available upon Customer's Request.

※ 운임 약 ₩ 9,000 별도!

Fa Price ₩

## Optional Platforms/Spring Racks

,	, 1	La. FIICE, W
DH.WSO604100 DH.WSO604200	(1) Universal Platform, w251 $\times$ d251mm (1) , w346 $\times$ d346mm	97,000 101,000
DH.WSO604110 DH.WSO604210	(2) Rubber Mat Platform, w295 $\times$ d295mm (2) , w370 $\times$ d370mm	48,000 56,000
DH.WSO604140 DH.WSO504240	(3) Universal Spring Rack, w295 $\times$ d295 $\times$ h100mm (3) , w370 $\times$ d370 $\times$ h100mm	192,000 279,000
DH.WSO604130 DH.WSO604230	(4) Platform for Round Flask, w350 $\times$ d260 $\times$ h153mm (5) Platform for Separatory Funnels, w350 $\times$ d260 $\times$ h153mm	157,000 159,000

The Details of Flask Holders: Please See 974Page

